

1-800-GRAINGER (472-4643)

For more information on Sockets, see page 730.

				Standard		Socket Depth	
Socket Size	Finish	Tether Ready	Brand	Overall Length	Item No.	Overall Length	Item No.
1/4" Drive Metric Sockets							
6-Point							
5.5-mm	Chrome	Yes	Westward	1 in	53YP88	—	—
6-mm	Chrome	Yes	Westward	1 in	53YP89	—	—
7-mm	Chrome	Yes	Westward	1 in	53YP90	—	—
7-mm	Chrome	No	SK Tools	7/8 in	13N766	2 in	12A276
8-mm	Chrome	Yes	Westward	1 in	53YP91	2 in	53YR36
8-mm	Chrome	No	SK Tools	7/8 in	13N767	2 in	12A277
8-mm	Chrome	No	Proto	7/8 in	429M33	1 5/8 in	429M30
9-mm	Chrome	Yes	Westward	—	—	2 in	53YR37
10-mm	Chrome	No	SK Tools	7/8 in	13N769	2 in	12A279
10-mm	Chrome	No	Proto	7/8 in	429M50	1 5/8 in	429M47
10-mm	Chrome	Yes	Westward	1 in	53YP93	2 in	53YR38
11-mm	Chrome	Yes	Westward	—	—	2 in	53YR39
13-mm	Chrome	No	SK Tools	7/8 in	13N772	2 in	12A282
12-Point							
7-mm	Chrome	Yes	Westward	1 in	53YR13	—	—
8-mm	Chrome	Yes	Westward	1 in	53YR14	2 in	53YR58
10-mm	Chrome	Yes	Westward	1 in	53YR16	2 in	53YR60
10-mm	Chrome	No	Proto	7/8 in	429M53	—	—
12-mm	Chrome	Yes	Westward	—	—	2 in	53YR62
13-mm	Chrome	No	Proto	7/8 in	429M74	—	—
3/4" Drive Metric Sockets							
6-Point							
4-mm	Chrome	No	SK Tools	1 3/4 in	12A262	—	—
5-mm	Chrome	No	SK Tools	1 3/4 in	12A263	—	—
7-mm	Chrome	No	Proto	27.8-mm	429N74	—	—
7-mm	Chrome	Yes	Westward	1 in	53YR79	—	—
8-mm	Chrome	Yes	Westward	1 in	53YR80	—	—
8-mm	Chrome	No	SK Tools	1 3/4 in	12P866	—	—
10-mm	Chrome	No	SK Tools	1 3/4 in	12P868	1 3/4 in	13N573
10-mm	Chrome	Yes	Westward	1 in	53YR82	2 1/2 in	53YT53
10-mm	Chrome	No	Proto	27.8-mm	429N85	—	—
11-mm	Chrome	Yes	Westward	1 in	53YR83	—	—
12-mm	Chrome	No	Proto	28.6-mm	429N93	—	—
12-mm	Chrome	Yes	Westward	1 in	53YR84	2 1/2 in	53YT55
12-mm	Chrome	No	SK Tools	1 3/4 in	12P870	1 3/4 in	13N575
12-mm	Chrome	No	Proto	—	—	2 1/2 in	429N27
13-mm	Chrome	No	SK Tools	1 3/4 in	12P871	1 3/4 in	13N576
13-mm	Chrome	Yes	Westward	1 in	53YR85	2 1/2 in	53YT56
13-mm	Chrome	No	Proto	28.6-mm	429N95	2 1/2 in	429N29
14-mm	Chrome	Yes	Westward	1 in	53YR86	—	—
14-mm	Chrome	No	Proto	28.6-mm	429N99	—	—
14-mm	Chrome	No	SK Tools	1 3/4 in	12P872	1 5/8 in	13N577
15-mm	Chrome	Yes	Westward	1 in	53YR87	—	—
15-mm	Chrome	No	SK Tools	1 3/4 in	12P873	1 5/8 in	13N578
15-mm	Chrome	No	Proto	28.6-mm	429P02	—	—
16-mm	Chrome	Yes	Westward	1 in	53YR88	—	—
17-mm	Chrome	No	SK Tools	1 3/4 in	12P875	2 1/2 in	13N580
17-mm	Chrome	Yes	Westward	1 in	53YR89	—	—
17-mm	Chrome	Yes	Westward	—	—	2 1/2 in	53YT60
17-mm	Chrome	No	Proto	—	—	2 3/4 in	429N41
18-mm	Chrome	Yes	Westward	1 in	53YR90	—	—
18-mm	Chrome	No	SK Tools	—	—	2 1/2 in	13N581
19-mm	Chrome	Yes	Westward	1 in	53YR91	—	—
19-mm	Chrome	No	SK Tools	1 3/4 in	12P876	2 1/2 in	13N582
19-mm	Chrome	No	Proto	—	—	2 3/4 in	429N47
20-mm	Chrome	No	SK Tools	—	—	2 1/2 in	20K678
12-Point							
8-mm	Chrome	No	Proto	1 3/2 in	429N77	—	—
8-mm	Chrome	No	Proto	—	—	2 1/2 in	429N13
8-mm	Chrome	Yes	Westward	—	—	2 1/2 in	53YT86
10-mm	Chrome	No	Proto	1 3/2 in	429N84	2 1/2 in	429N19
10-mm	Chrome	Yes	Westward	1 in	53YT18	2 1/2 in	53YT88
10-mm	Chrome	No	Proto	1 3/4 in	483H76	—	—
10-mm	Chrome	No	SK Tools	1 3/4 in	12P885	1 3/4 in	13N583
11-mm	Chrome	No	Proto	1 3/4 in	483H78	—	—
13-mm	Chrome	No	Proto	1 1/2 in	429N94	—	—
13-mm	Chrome	Yes	Westward	1 in	53YT21	2 1/2 in	53YT91
13-mm	Chrome	No	Proto	1 5/8 in	483H82	—	—
13-mm	Chrome	No	SK Tools	1 3/4 in	20K801	—	—
13-mm	Chrome	No	Proto	—	—	2 1/2 in	429N28
14-mm	Chrome	No	SK Tools	—	—	1 5/8 in	13N587
15-mm	Chrome	Yes	Westward	1 in	53YT23	2 1/2 in	53YT93
15-mm	Chrome	No	Proto	—	—	2 3/4 in	429N34
17-mm	Chrome	No	Proto	1 1/2 in	429P07	2 3/4 in	429N40
17-mm	Chrome	Yes	Westward	1 in	53YT25	2 1/2 in	53YT95
17-mm	Chrome	No	SK Tools	—	—	2 1/2 in	13N590
19-mm	Chrome	Yes	Westward	—	—	2 1/2 in	53YT97
19-mm	Chrome	No	Proto	—	—	2 3/4 in	429N46
1/2" Drive Metric Sockets							
6-Point							
13-mm	Chrome	No	SK Tools	—	—	3 1/4 in	13N706
17-mm	Chrome	No	SK Tools	1 3/4 in	12C438	3 1/4 in	13N710
19-mm	Chrome	No	SK Tools	1 1/2 in	12C440	—	—
19-mm	Chrome	Yes	Westward	1 1/2 in	5MT42	—	—
19-mm	Chrome	Yes	Westward	—	—	3 in	53YV10
21-mm	Chrome	No	SK Tools	—	—	3 1/4 in	20K037
22-mm	Chrome	No	Proto	1 1/2 in	429R47	—	—
22-mm	Chrome	Yes	Westward	1 1/2 in	53YU34	—	—
22-mm	Chrome	No	SK Tools	—	—	3 1/4 in	20K038
24-mm	Chrome	No	SK Tools	1 5/8 in	12C445	3 1/4 in	20K040
24-mm	Chrome	Yes	Westward	1 1/2 in	53YU36	—	—
24-mm	Chrome	No	Proto	1 1/2 in	429R53	—	—
24-mm	Chrome	Yes	Westward	—	—	3 in	53YV15
27-mm	Chrome	No	SK Tools	1 3/2 in	20K564	3 1/4 in	20K043
30-mm	Chrome	No	SK Tools	1 3/2 in	20K567	3 1/4 in	20K045
30-mm	Chrome	Yes	Westward	1 1/2 in	53YU42	3 in	53YV21

53YR80



**SK** **PROTO** **WESTWARD**

## All Purpose Metric Sockets

				Socket Depth			
				Standard		Deep	
Socket Size	Finish	Tether Ready	Brand	Overall Length	Item No.	Overall Length	Item No.
30-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>2</sub> in	429R71	—	—
32-mm	Chrome	No	SK Tools	1 <sup>3</sup> / <sub>2</sub> in	20K568	—	—
34-mm	Chrome	No	Proto	1 <sup>7</sup> / <sub>8</sub> in	429R80	—	—
36-mm	Chrome	No	Proto	2 <sup>1</sup> / <sub>4</sub> in	429R84	—	—
36-mm	Chrome	No	SK Tools	1 <sup>3</sup> / <sub>2</sub> in	20K569	—	—
12-Point							
10-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>4</sub> in	429R10	—	—
13-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>4</sub> in	429R18	—	—
13-mm	Chrome	No	Proto	—	—	3 <sup>1</sup> / <sub>4</sub> in	429P58
17-mm	Chrome	No	Proto	1 <sup>1</sup> / <sub>2</sub> in	429R30	—	—
18-mm	Chrome	No	Proto	1 <sup>1</sup> / <sub>2</sub> in	429R34	3 <sup>1</sup> / <sub>4</sub> in	429P69
19-mm	Chrome	No	Proto	1 <sup>1</sup> / <sub>2</sub> in	429R36	3 <sup>1</sup> / <sub>4</sub> in	429P70
19-mm	Chrome	Yes	Westward	1 <sup>1</sup> / <sub>2</sub> in	53YU70	—	—
21-mm	Chrome	No	Proto	1 <sup>1</sup> / <sub>2</sub> in	429R42	3 <sup>1</sup> / <sub>4</sub> in	429P74
22-mm	Chrome	No	Proto	—	—	3 <sup>1</sup> / <sub>4</sub> in	429P77
24-mm	Chrome	No	Proto	1 <sup>1</sup> / <sub>2</sub> in	429R52	3 <sup>1</sup> / <sub>4</sub> in	429P81
24-mm	Chrome	Yes	Westward	1 <sup>1</sup> / <sub>2</sub> in	53YU75	—	—
24-mm	Chrome	No	SK Tools	1 <sup>5</sup> / <sub>8</sub> in	13N751	—	—
24-mm	Chrome	Yes	Westward	—	—	3 in	53YV54
27-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>4</sub> in	429R60	—	—
30-mm	Chrome	Yes	Westward	1 <sup>1</sup> / <sub>2</sub> in	53YU81	—	—
30-mm	Chrome	Yes	Proto	—	—	3 <sup>1</sup> / <sub>4</sub> in	49XG10
30-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>2</sub> in	429R70	3 <sup>1</sup> / <sub>4</sub> in	429P93
32-mm	Chrome	No	Proto	—	—	3 <sup>1</sup> / <sub>4</sub> in	429P97
34-mm	Chrome	No	Proto	1 <sup>3</sup> / <sub>2</sub> in	19C426	—	—
36-mm	Chrome	Yes	Proto	2 <sup>1</sup> / <sub>4</sub> in	24AH99	—	—
36-mm	Chrome	No	Proto	2 <sup>1</sup> / <sub>4</sub> in	429R83	3 <sup>1</sup> / <sub>4</sub> in	6RCT2
36-mm	Chrome	No	SK Tools	1 <sup>3</sup> / <sub>2</sub> in	20K554	—	—
38-mm	Chrome	No	Proto	2 <sup>1</sup> / <sub>4</sub> in	6RCR6	—	—
3/4" Drive Metric Sockets							
6-Point							
22-mm	Chrome	Yes	Westward	2 in	10E318	—	—
24-mm	Chrome	Yes	Westward	2 in	10E320	3 <sup>1</sup> / <sub>4</sub> in	10E342
27-mm	Chrome	Yes	Westward	—	—	3 <sup>1</sup> / <sub>4</sub> in	10E344
30-mm	Chrome	Yes	Westward	2 <sup>5</sup> / <sub>8</sub> in	10E325	3 <sup>1</sup> / <sub>4</sub> in	10E347
32-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	10E326	3 <sup>1</sup> / <sub>4</sub> in	10E348
35-mm	Chrome	Yes	Westward	—	—	3 <sup>1</sup> / <sub>4</sub> in	10E349
36-mm	Chrome	Yes	Westward	2 <sup>5</sup> / <sub>8</sub> in	10E328	3 <sup>1</sup> / <sub>4</sub> in	10E350
38-mm	Chrome	Yes	Westward	—	—	3 <sup>1</sup> / <sub>4</sub> in	10E351
41-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>2</sub> in	10E330	3 <sup>1</sup> / <sub>4</sub> in	10E352
42-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>2</sub> in	10E331	3 <sup>1</sup> / <sub>4</sub> in	10E353
46-mm	Chrome	Yes	Westward	2 <sup>5</sup> / <sub>8</sub> in	10E332	3 <sup>1</sup> / <sub>4</sub> in	10E354
50-mm	Chrome	Yes	Westward	2 <sup>3</sup> / <sub>4</sub> in	10E333	3 <sup>1</sup> / <sub>4</sub> in	10E355
55-mm	Chrome	Yes	Westward	3 in	10E335	3 <sup>1</sup> / <sub>4</sub> in	10E357
60-mm	Chrome	Yes	Westward	3 <sup>1</sup> / <sub>2</sub> in	10E337	3 <sup>1</sup> / <sub>4</sub> in	10E358
12-Point							
24-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	5MX47	—	—
27-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	5MX49	—	—
30-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	5MX51	—	—
36-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	5MX54	—	—
36-mm	Satin	No	Proto	2 <sup>1</sup> / <sub>2</sub> in	429T17	—	—
41-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>2</sub> in	5MX56	—	—
41-mm	Satin	No	Proto	2 <sup>3</sup> / <sub>4</sub> in	429T20	—	—
46-mm	Chrome	Yes	Westward	2 <sup>3</sup> / <sub>4</sub> in	5MX57	—	—
46-mm	Satin	No	Proto	2 <sup>3</sup> / <sub>2</sub> in	429T24	—	—
50-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	5MX58	—	—
54-mm	Chrome	No	Proto	3 <sup>3</sup> / <sub>2</sub> in	1AP84	—	—
55-mm	Chrome	Yes	Westward	76-mm	20HW72	—	—
55-mm	Satin	No	Proto	3 <sup>3</sup> / <sub>2</sub> in	429T30	—	—
60-mm	Satin	No	Proto	3 <sup>3</sup> / <sub>2</sub> in	429T34	—	—
1" Drive Metric Sockets							
12-Point							
36-mm	Chrome	Yes	Westward	2 <sup>1</sup> / <sub>4</sub> in	45J241	—	—
46-mm	Chrome	Yes	Westward	3 in	45J244	—	—
46-mm	Satin	No	Proto	2 <sup>1</sup> / <sub>4</sub> in	19C401	—	—
50-mm	Satin	No	Proto	3 in	19C402	—	—
55-mm	Chrome	Yes	Westward	3 <sup>3</sup> / <sub>2</sub> in	45J247	—	—
55-mm	Satin	No	Proto	3 <sup>1</sup> / <sub>4</sub> in	19C404	—	—
60-mm	Chrome	Yes	Westward	3 <sup>1</sup> / <sub>2</sub> in	45J249	—	—
63-mm	Satin	No	Proto	3 <sup>1</sup> / <sub>2</sub> in	19C407	—	—
65-mm	Chrome	Yes	Westward	3 <sup>1</sup> / <sub>2</sub> in	45J251	—	—
65-mm	Satin	No	Proto	3 <sup>1</sup> / <sub>2</sub> in	19C408	—	—
67-mm	Chrome	Yes	Westward	3 <sup>1</sup> / <sub>2</sub> in	45J252	—	—
70-mm	Chrome	Yes	Westward	3 <sup>3</sup> / <sub>4</sub> in	45J253	—	—
75-mm	Chrome	Yes	Westward	3 <sup>3</sup> / <sub>2</sub> in	45J255	—	—
77-mm	Chrome	Yes	Westward	4 in	45J256	—	—
80-mm	Chrome	Yes	Westward	4 in	45J257	—	—